



Sanitary Accessories

System Spacer

Oseco's spacers are designed with a standard ferrule connection rather than using a proprietary holder. The spacers can be used to place sensors downstream of a rupture disc when a separate rupture disc and sensor is required.

Oseco's spacers are made from 316L Stainless Steel and come standard with a 20 Ra finish on the inside diameter (32 Ra on the O.D.) The spacers are rated up to 1500 psig and 900° F (rating of tube only-derate to fitting and gasket capability). All parts come marked with lot/heat numbers for traceability. Electropolishing is available.

Available in sizes 1" to 4". Length of spacers are made to match the most common industry holder sizes. Custom sizes available upon request. **Each spacer includes two Oseco tri-clamps.**



System Spacer Sizes

CLAMP SIZE (inches)	HEIGHT (inches)	PART NUMBER
1	1.62	X60-0109-001
1.5	1.62	X60-1509-001
2	1.62	X60-0209-001
3	1.81	X60-0309-001
4	2.25	X60-0409-001

Oseco Inc
1701 W. Tacoma
Broken Arrow Oklahoma 74012 USA
Tel: (918) 258-5626
Fax: (918) 251-2809

Visit the products section of oseco.com to ensure you have the most recent information.



www.oseco.com

Contact Oseco at **800-395-3475**
or email us at info@oseco.com.



Sanitary Accessories

Tri-Clamps • SANITARY DISCS

Tri-Clamps

Oseco offers a 304 stainless steel tri-clamp fitting model 13MHMD for use with sensors and rupture discs. All clamps include a 316 stainless steel 3/4" hex nut for use with any standard torque wrench. Available in sizes 1" to 4". High pressure clamps available for special applications.



Tri-Clamps Sizes

CLAMP SIZE (inches)	PSI rating at 72° F	PART NUMBER
1 & 1.5	500	X59-0109-001
2	450	X59-0209-001
3	350	X59-0309-001
4	300	X59-0409-001

Oseco Inc

1701 W. Tacoma
Broken Arrow Oklahoma 74012 USA
Tel: (918) 258-5626
Fax: (918) 251-2809

Visit the products section of oseco.com to ensure you have the most recent information.



www.oseco.com

Contact Oseco at 800-395-3475
or email us at info@oseco.com.

0910